



Bandpass Filters for Biophotonics

Steep Edge Bandpass Filters for Fluorescence and Raman Detection

Materion Balzers Optics bandpass filters excel by steep transition between blockband and passband and high passband transmittance. The all-dielectric interference filters are deposited by plasma-assisted processes and show extreme environmental stability. Our sophisticated filter designs are optimized according to the requirements of the application.



Benefits

- Sharp separation between blockband and passband
- High transmittance > 90 % outside the blockband
- Long-term shift-free spectral performance
- High environmental stability
- Wide flexibility in filter size

Applications

- Fluorescence detection
- Raman spectroscopy
- Excitation filters for LED and lasers

Technical Data

Passband wavelength

240 – 2000 nm

Blocking

OD5 to OD6, depending on requirements

Transmittance

> 90 – 95 % outside blockband

Angle of incidence

Standard 0°, different AOI on request

Substrate material

Fused silica or BK7

Dimensions

Standard size Ø 25 mm, thickness 3 mm,
other dimensions on request

Parallelism

< 3 arcmin


Surface defects

5 / 3 x 0.16

Environmental stability

Temperature -40 °C to +300 °C

Humidity up to 99 %



Optics Balzers Jena GmbH
Otto-Eppenstein-Strasse 2
07745 Jena

Deutschland
T +49 3641 3529 30
F +49 3641 3529 35
info.mbo@materion.com
www.materion.com/balzersoptics

All-dielectric bandpassfilter for the VIS range with OD5 blocking




Fig. 1: Measured spectral transmittance, passband

All-dielectric bandpassfilter for the VIS range with OD5 blocking




Fig. 2: Measured spectral transmittance, blockband

Shortpass 400 nm with OD5 blocking




Fig. 3: Measured spectral transmittance

Multi-Bandpass 420 – 475 / 500 – 610 nm




Fig. 4: Measured spectral transmittance,
OD 5 blocking for 350-410, 488, 630-800 nm

Optics Balzers Jena GmbH
Otto-Eppenstein-Strasse 2
07745 Jena

Deutschland
T +49 3641 3529 30
F +49 3641 3529 35
info.mbo@materion.com
www.materion.com/balzersoptics